

# Upright Dustpan and Broom Set

330 mm, Medium, Grey



Item Number: 566688

The contact lip is designed for easy and efficient sweeping into the dustpan. The outer front surface has a raised area to prevent debris from falling out of the dustpan. The enlarged rear and side walls enable the dustpan to hold larger volumes of debris. The very effective, lightweight broom can be used for sweeping both dry and wet debris. The brush pattern is designed using 2 filament diameters. The outer row of filaments is softer than the middle row, which gives a very effective sweeping quality. The filaments under the scraping edge are angled to facilitate sweeping close to walls and corners as well as under workbenches etc. An effective scraping edge has been implemented in the design to enable loosening stubborn debris from the surface.

## General Information

Bristle stiffness	Medium
Colour	Grey
Material	Polypropylene, Anodised Aluminium, Polyamide, Polyester (PBT)
Country of Origin	Denmark

## Product Dimensions

Product Length/Depth	330 mm
Product Width	200 mm
Product Height	880 mm
Net Weight	0.82 kg

## Packaging & Shipping Details

Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x approx.180 cm)	120 Pcs.
Quantity Per Layer (Pallet)	20 Pcs.
Box Length/Depth	1000 mm
Box Width	410 mm
Box Height	260 mm
Plastic Packaging (Recycling Symbol "4") LDPE per Pcs.	0.06 kg
Cardboard Packaging (Recycling symbol "20" PAP) per Pcs.	0.0668 kg
Total Tare Weight	0.1268 kg
Gross Weight	0.95 kg
Cubic metre	0.05808 M3
GTIN-13 Number	5705022044623
GTIN-14 Number (Box quantity)	15705028044631
Customs Tariff Number	96039099

Item Number: 566688

## Compliance & Standard Details

Complies with (EC) 1935/2004 on food contact materials <sup>1</sup>	Yes
Complies with EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
Complies with FDA Regulation CFR 21 <sup>1</sup>	Yes
Complies with UK 2019 No. 704 on food contact materials	Yes
Complies with REACH Regulation (EC) No. 1907/2006	Yes
Complies with California Proposition 65	Yes
Complies with Halal and Kosher	Yes
PFAS intentionally added	No

## Usage Limits

Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature <sup>3</sup>	-20 °C
Max. drying temperature	100 °C

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.

